

Technical Data Sheet

Transtar's Aqua SCAT 2 Waterborne Degreaser is a specially formulated, water-based degreaser that can be used on all plastics, metal and pre-painted parts. Its unique mix of alcohol, surfactants and water make it ideal for cleaning and degreasing plastics prior to painting or priming. Aqua SCAT 2 also reduces the amount of dust contact by neutralizing static charge. Compliant across North America.

SUITABLE SUBSTRATES

Substrate		Substrate		Substrate	
Bare Steel	~	Raw Plastic - Rigid (SMC, BMC) +	\checkmark	Primer - Self-Etching	✓
Bare Galvanized	~	Raw Plastic - Flexible (ABD, PPO) +	\checkmark	Primer - 1K	\checkmark
Bare Aluminum	\checkmark	Raw Plastic - Soft (PUR) +	\checkmark	Primer - 2K	\checkmark
OEM E-Coat**	~	Plastic Part - Primed ++	\checkmark	OEM Finish & Old Paint Work - Reversible	\checkmark
Fiberglass/SMC Unbroken Gel Coat	✓	Body Filler	\checkmark	OEM Finish & Old Paint Work - Non-Reversible	\checkmark

MIXING



Mix Ratio: Ready to Spray

Pot Life: N/A

SURFACE PREPARATION

Apply Aqua SCAT 2 to surface prior to grinding, sanding or painting to prevent contaminants from being worked into the substrate surface.

APPLICATION



Ready to use. Spray or wipe on substrate. Wipe off with LINT-FREE cloth.

Note: Re-wiping (i.e. with tack cloth) after using Aqua SCAT 2 may increase static.

Aqua SCAT 2 can be used in your current multi-step process as a degreaser. It can also be used as a one-step process as an antistatic and degreaser.

PRODUCT SPECIFICATIONS

Color: Clear Liquid	Shelf Life: 1 year
Size: Gallon (1391), Quart (1394)	

REGULATORY:

Category: Cleaner/Surface	1391/1394	Weight % of Exempt Compounds	1.5
Preparation		Volume % of Exempt Compounds	1.87
VOC Actual	0.21#/gal (25 g/l)	Density of Material #/gal	8.26
VOC Regulatory	5.01#/gal (600 g/l)		
Weight % of Volatiles	99		
Weight % of Water	95		

LIMITATIONS & PRECAUTIONS

For use only by professional, trained painters. Not for sale to or use by the general public.

Before use, read and follow all TDS, label and SDS precautions.

Visit www.tat-co.com to assure you are using most updated TDS, to view in other languages and for links to Standard Operating Procedures (SOPs). TRANSTAR AUTOBODY TECHNOLOGIES • 2040 HEISERMAN DRIVE, BRIGHTON, MI 48114 • (800) 824-2843